


# Case Style

# QE

## Outline Dimensions

## QE2249



- Instruction for mounting bracket:
1. Tool required: Phillips head screwdriver
  2. Mount the bracket over threaded holes on the bottom side with the fasteners provided with the bracket.

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q
QE2249	3.00 (76.2)	5.17 (131.3)	.85 (21.6)	.28 (7.1)	.50 (12.7)	.89 (22.6)	2.700 (68.58)	4.870 (123.70)	2.850 (72.39)	3.280 (83.31)	3.75 (95.25)	3.375 (85.73)	.188 (4.76)	2.400 (60.96)	.185 (4.70)

CASE#	R	S	T	WT. GRAMS
QE2249	.144 (3.66)	100 (2.54)	.185 (4.70)	400

### Notes:

1. Case material: Aluminum.
2. Case finish: Clear chemical conversion coating, non-chrome or trivalent chrome based.

**Mini-Circuits®**

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified