


### Outline Dimensions



\* OVERALL CONNECTOR OR CABLE & BOOT DIM  
[CONNECTOR SHAPE MAY VARY]

RH2515 SERIES  
2.4mm MALE (CONN-1)  
2.4mm FEMALE (CONN-2)

CASE STYLE #	A		B	C	D	E	F	T		WEIGHT GRAMS				
	FEET	METERS						INCH	MM					
RH2515-2	2.00	.61	.79 (20.0)	.315 (8.00)	.83 (21.00)	.75 (19.00)	.602 (15.3)	+.787/-0	+20.0/-0	328				

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. High Performance rugged Cable.