


### Outline Dimensions



\* OVERALL CONNECTOR OR CABLE & BOOT DIM  
[CONNECTOR SHAPE MAY VARY]

#### RK2525 SERIES

2.92mm MALE (CONN-1)

2.92mm MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	F	T		WEIGHT GRAMS
	FEET	METERS						INCH	MM	
RK2525-2	2.00	.61	.36 (9.25)	.315 (8.00)	.36 (9.25)	.315 (8.00)	.142 (3.60)	+.08/-0	+2.0/-0	49
RK2525-3	3.00	.91						+.08/-0	+2.0/-0	60

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

#### Note:

1. Low Loss Flexible (T40) Cable.