


Outline Dimensions



* OVERALL CONNECTOR OR CABLE & BOOT DIM
[CONNECTOR SHAPE MAY VARY]

RK2526 SERIES

2.4mm FEMALE (CONN-1)

2.4mm MALE (CONN-2)

| CASE STYLE # | A | | B | C | D | E | F | T | | WEIGHT GRAMS | | | |
|--------------|------|--------|---------------|----------|---------------|----------------|----------------|---------|---------|--------------|--|--|--|
| | FEET | METERS | | | | | | INCH | MM | | | | |
| RK2526-2 | 2.00 | .61 | .36 (9.25) | -- -- | .36 (9.25) | .315 (8.00) | .142 (3.60) | +.08/-0 | +2.0/-0 | 47 | | | |
| RK2526-3 | 3.00 | .91 | | | | | | +.08/-0 | +2.0/-0 | 58 | | | |
| | | | | | | | | | | | | | |
| | | | | | | | | | | | | | |
| | | | | | | | | | | | | | |
| | | | | | | | | | | | | | |

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Note:

1. Low Loss Flexible (T40) Cable.