


### Outline Dimensions



\* OVERALL CONNECTOR DIMENSION

#### SG2637 SERIES SMA MALE (CONN)

CASE STYLE #	A		B	C1	C2	D	E1	E2	F FL141-ASM+	T		WEIGHT GRAMS
	INCH	MM								INCH	MM	
SG2637-6	6	152.4	.36 (9.14)	.315 (8.0)	-	.36 (9.14)	.315 (8.0)	-	.163±.006 (4.14±0.15)	0.05	1.27	8.11
SG2637-9	9	228.6								0.10	2.54	14.56
SG2637-12	12	304.8								0.10	2.54	17.88
SG2637-24	24	609.6								0.15	3.81	31.17

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

#### Note:

1. 141 Flexible Coaxial Cable.
2. "A" Represents Length of Cable.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS