


Outline Dimensions

YR3342



CASE#	A	B	C	D	E	F	G	H	J	K	L	WT.GRAM
YR3342	.210 (5.33)	1.200 (30.48)	.030 (0.76)	.105 (2.67)	.015 (0.38)	.020 (0.51)	.015 (0.38)	.106 (2.70)	.021 (0.54)	.213 (5.40)	1.203 (30.54)	0.35

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3Pl. $\pm .005$

Notes:

1. Base: Printed wiring laminate.
2. Termination finish:
For RoHS Case Styles: 3-5 μ inch gold over 120-240 μ inch nickel plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS