

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.07	39.3	38.9
200.0	0.10	41.6	41.7
400.0	0.15	41.8	42.2
500.0	0.17	43.3	42.3
700.0	0.20	42.9	44.4
800.0	0.22	42.7	43.3
1000.0	0.25	43.4	44.1
1100.0	0.26	41.9	41.6
1500.0	0.31	51.2	45.6
1750.0	0.33	40.9	41.8
2000.0	0.36	39.2	40.9
2250.0	0.39	41.2	44.3
2500.0	0.41	48.4	46.8
2750.0	0.43	38.6	41.0
3000.0	0.45	35.2	38.8
3250.0	0.47	40.4	43.5
3750.0	0.51	34.2	36.0
4000.0	0.52	32.8	35.3
4250.0	0.54	38.6	46.1
4500.0	0.56	37.3	38.9
5000.0	0.59	33.2	37.7
5500.0	0.62	31.7	32.8
6000.0	0.64	33.4	38.2
6500.0	0.68	31.0	31.9
7000.0	0.70	32.8	36.7
7500.0	0.73	35.1	36.6
8000.0	0.75	34.8	37.4
8500.0	0.78	33.7	34.3
9000.0	0.81	30.4	31.2
9500.0	0.83	35.8	36.5
10000.0	0.86	26.6	27.6
10500.0	0.87	30.7	29.9
11000.0	0.90	24.5	25.4
11500.0	0.92	28.3	31.3
12000.0	0.96	21.2	21.8
12500.0	0.95	32.6	34.5
13000.0	1.01	20.9	21.9
13500.0	1.00	33.5	30.0
14000.0	1.06	19.9	20.7
14500.0	1.04	27.2	26.9
15000.0	1.09	22.1	23.2
15500.0	1.10	24.2	24.4
16000.0	1.12	25.6	28.0
16500.0	1.14	25.6	25.8
17000.0	1.17	24.0	24.7
17500.0	1.19	22.8	23.5
18000.0	1.21	22.7	23.1