

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10	0.06	57.5	52.6
50	0.04	42.2	41.0
100	0.07	40.0	39.8
200	0.11	41.8	43.3
300	0.14	62.2	50.4
400	0.16	46.0	43.6
500	0.18	44.9	45.2
500	0.18	44.9	45.2
1000	0.25	43.9	49.5
1500	0.31	51.1	47.4
2000	0.36	39.7	47.4
2500	0.40	40.3	40.5
3000	0.43	41.6	50.9
3500	0.47	40.9	39.5
4000	0.51	37.9	44.7
4500	0.54	40.9	39.8
5000	0.57	34.4	35.5
5500	0.60	35.1	36.3
6000	0.62	34.0	34.2
6500	0.65	39.0	39.7
7000	0.68	30.7	31.0
7500	0.70	37.9	40.2
8000	0.72	35.4	34.2
8500	0.74	35.8	35.9
9000	0.77	33.9	33.2
9500	0.80	29.4	29.5
10000	0.82	32.5	31.0
10500	0.85	26.8	26.6
11000	0.87	27.7	27.4
11500	0.89	25.7	25.3
12000	0.91	28.7	28.1
12500	0.94	25.1	25.1
13000	0.94	35.2	32.6
13500	0.97	28.3	27.7
14000	0.98	38.7	34.7
14500	1.02	24.6	24.5
15000	1.02	46.1	35.5
15500	1.05	25.7	25.8
16000	1.06	37.6	38.4
16500	1.09	25.5	25.3
17000	1.10	33.0	31.2
17500	1.12	33.0	33.7
18000	1.15	27.9	28.9

