

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
100.0	0.08	42.4	42.9
200.0	0.12	42.4	41.9
300.0	0.15	48.3	47.1
400.0	0.17	44.1	42.7
500.0	0.20	39.5	39.3
600.0	0.22	46.8	45.0
700.0	0.24	41.3	40.9
800.0	0.26	37.5	37.2
1000.0	0.29	37.4	37.5
1100.0	0.31	36.2	36.1
1300.0	0.34	35.6	36.4
1400.0	0.35	35.9	35.9
1600.0	0.38	34.1	34.5
1700.0	0.39	37.4	37.3
1800.0	0.40	37.8	40.1
1900.0	0.41	31.7	32.0
2000.0	0.43	37.2	37.3
2500.0	0.48	31.4	31.6
3000.0	0.53	30.0	31.2
3500.0	0.58	32.6	35.9
4000.0	0.62	32.5	34.2
4500.0	0.67	28.1	28.6
5000.0	0.71	26.7	27.4
5500.0	0.74	31.9	35.2
6000.0	0.77	34.8	40.5
6500.0	0.81	30.8	31.9
7000.0	0.84	30.8	32.3
7500.0	0.88	31.5	34.6
8000.0	0.91	34.4	36.6
8500.0	0.93	32.6	34.3
9000.0	0.97	31.4	35.1
9500.0	0.98	31.0	37.5
10000.0	1.01	26.5	28.9
10500.0	1.03	26.7	28.2
11000.0	1.02	29.5	34.2
11500.0	1.03	29.5	44.3
12000.0	1.05	25.3	26.3
12500.0	1.04	22.4	22.9
13000.0	0.93	23.3	24.0
13500.0	0.92	27.4	28.9
14000.0	0.86	25.9	36.3
15000.0	0.94	24.0	23.2
16000.0	0.90	27.5	30.9
16500.0	1.10	32.8	29.6
17000.0	1.21	25.7	25.6
17500.0	1.27	28.5	32.1
18000.0	1.34	25.7	26.6