

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92MM-MALE 1 RETURN LOSS (dB)	2.92MM-MALE 2 RETURN LOSS (dB)
100	0.21	24.8	45.3
200	0.21	38.3	38.9
300	0.25	29.0	35.9
400	0.30	33.2	35.4
500	0.31	31.4	38.2
600	0.31	28.2	35.6
700	0.34	43.7	40.6
800	0.40	28.5	31.4
900	0.39	48.0	40.6
1000	0.41	30.3	32.7
2000	0.62	31.8	30.4
3000	0.80	36.2	34.2
4000	0.94	30.4	31.3
5000	1.07	33.2	32.3
6000	1.17	30.8	30.0
7000	1.27	31.1	28.1
8000	1.36	27.9	33.0
9000	1.50	31.0	30.2
10000	1.56	26.0	22.3
11000	1.63	27.1	25.6
12000	1.74	29.6	28.9
13000	1.83	33.9	35.1
14000	1.97	28.6	31.8
15000	2.01	25.7	27.3
16000	2.08	33.2	34.3
17000	2.20	32.9	29.3
18000	2.28	33.3	25.7
19000	2.33	34.1	28.8
20000	2.41	22.1	24.1
21000	2.48	20.7	22.1
22000	2.56	27.7	46.0
23000	2.68	24.1	23.2
24000	2.74	37.2	32.2
25000	2.84	28.8	28.7
26000	2.94	23.0	25.1
27000	3.05	22.5	30.2
28000	3.05	22.4	23.8
29000	3.12	22.9	22.5
30000	3.21	25.5	22.5
31000	3.25	52.4	32.1
32000	3.32	30.3	33.4
33000	3.38	22.1	23.9
34000	3.50	25.0	35.0
35000	3.54	24.2	36.6
36000	3.65	31.5	39.7
37000	3.63	32.0	34.4
38000	3.77	29.5	33.6
39000	3.83	29.3	37.3
40000	3.90	27.0	39.2