

Hand-Flex Coaxial Cable

141-14SMRSM+

SMA Male to Right Angle SMA Male

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
100.0	0.03	36.8	37.0
200.0	0.06	36.2	36.1
300.0	0.07	51.1	50.4
400.0	0.09	33.8	34.4
500.0	0.10	36.4	36.1
600.0	0.11	45.1	45.7
700.0	0.12	33.6	33.6
800.0	0.13	36.8	36.5
900.0	0.14	41.8	42.7
1000.0	0.15	33.3	33.2
1100.0	0.16	38.6	38.5
1200.0	0.17	38.3	38.9
1300.0	0.17	31.9	31.7
1400.0	0.18	37.3	36.3
1500.0	0.18	37.4	38.4
1600.0	0.20	31.7	31.5
1700.0	0.21	37.0	35.5
1800.0	0.21	37.7	39.2
1900.0	0.22	32.1	32.3
2000.0	0.22	38.5	36.7
2400.0	0.24	38.9	41.3
3000.0	0.28	37.8	39.5
4000.0	0.34	30.8	31.4
5000.0	0.37	37.4	36.6
6000.0	0.41	36.8	35.7
7000.0	0.46	34.9	34.6
8000.0	0.49	40.2	36.8
9000.0	0.54	31.2	30.8
10000.0	0.55	40.4	55.6
11000.0	0.60	37.1	40.8
12000.0	0.66	30.2	29.0
13000.0	0.67	43.4	31.9
14000.0	0.72	27.6	28.8
15000.0	0.76	26.8	25.6
16000.0	0.83	20.3	20.6
17000.0	0.81	26.1	30.4
18000.0	0.92	20.4	19.9

