

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100.0	0.08	47.7	45.5
200.0	0.10	47.9	46.7
300.0	0.12	48.1	47.6
400.0	0.14	47.5	47.9
500.0	0.15	47.0	46.5
600.0	0.17	47.5	47.3
700.0	0.18	46.7	45.6
800.0	0.20	46.6	46.6
900.0	0.21	44.5	43.6
1000.0	0.22	44.5	44.7
1100.0	0.23	43.2	42.4
1200.0	0.24	44.0	44.2
1300.0	0.25	44.1	43.9
1400.0	0.26	44.0	43.7
1500.0	0.27	43.8	43.5
1600.0	0.28	43.6	42.5
1700.0	0.28	44.1	42.6
1800.0	0.29	42.8	40.9
1900.0	0.30	45.2	44.2
2000.0	0.31	45.3	46.4
2500.0	0.35	41.9	39.9
3000.0	0.38	40.3	38.4
4000.0	0.44	38.3	37.3
5000.0	0.51	36.6	37.3
6000.0	0.57	34.2	35.7
7000.0	0.61	37.8	41.1
8000.0	0.66	40.0	40.1
9000.0	0.70	39.6	40.4
10000.0	0.79	33.8	34.2
11000.0	0.84	36.0	35.7
12000.0	0.85	32.0	33.0
13000.0	0.91	30.3	30.4
14000.0	0.95	31.3	31.0
15000.0	1.01	29.7	28.4
16000.0	1.03	29.1	28.2
17000.0	1.13	27.1	24.8
18000.0	1.19	23.9	21.9

