

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
100.0	0.02	48.5	47.4
200.0	0.02	42.4	41.8
300.0	0.03	39.8	39.2
400.0	0.04	39.1	38.0
500.0	0.04	40.6	39.2
600.0	0.04	44.0	41.6
700.0	0.05	51.2	48.4
800.0	0.05	47.4	49.1
900.0	0.05	41.4	41.8
1000.0	0.06	38.2	37.9
1100.0	0.06	36.9	36.3
1200.0	0.07	36.7	35.8
1300.0	0.07	37.5	36.3
1400.0	0.07	40.3	38.6
1500.0	0.07	44.8	42.9
1600.0	0.08	46.5	46.3
1700.0	0.08	41.7	41.5
1800.0	0.08	38.2	37.5
1900.0	0.09	36.4	35.3
2000.0	0.09	35.6	34.4
2400.0	0.10	40.8	40.4
3000.0	0.11	37.5	35.8
4000.0	0.13	38.8	37.6
5000.0	0.16	34.9	34.6
6000.0	0.16	32.7	34.1
7000.0	0.18	34.3	35.1
8000.0	0.19	38.2	35.8
9000.0	0.21	29.9	30.4
10000.0	0.23	26.7	27.2
11000.0	0.24	28.1	27.5
12000.0	0.25	31.8	33.9
13000.0	0.24	29.4	29.8
14000.0	0.26	24.8	30.0
15000.0	0.27	24.9	36.8
16000.0	0.26	31.5	34.5
17000.0	0.29	28.5	26.4
18000.0	0.29	26.0	26.7