

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10.0	0.01	36.96	37.46
50.0	0.02	59.24	63.90
500.0	0.05	38.81	37.57
600.0	0.05	41.01	39.99
700.0	0.05	47.23	46.46
800.0	0.06	55.95	51.68
900.0	0.06	42.46	41.07
1000.0	0.07	38.62	37.41
1100.0	0.07	37.17	36.32
1250.0	0.07	37.72	37.89
1500.0	0.08	47.50	52.16
1750.0	0.09	39.10	40.99
2000.0	0.10	38.26	45.76
2001.0	0.09	38.25	45.73
2250.0	0.10	43.15	60.66
2500.0	0.11	43.39	42.05
2750.0	0.11	37.47	39.87
3000.0	0.12	39.58	40.29
3250.0	0.12	48.81	50.03
3500.0	0.14	36.29	39.93
3750.0	0.13	39.41	37.84
4000.0	0.14	45.21	39.68
4250.0	0.14	36.30	39.38
4500.0	0.15	38.53	48.19
4750.0	0.17	37.41	35.14
5000.0	0.17	33.67	41.40
5250.0	0.17	40.39	34.15
5500.0	0.18	34.45	32.69
5750.0	0.20	33.94	33.41
6000.0	0.20	39.13	37.05
6500.0	0.20	32.94	31.07
7000.0	0.23	32.36	30.36
7500.0	0.22	52.31	37.38
8000.0	0.22	33.13	33.14
8500.0	0.26	32.27	35.41
9000.0	0.25	37.29	37.66
9500.0	0.26	34.35	34.84
10000.0	0.24	32.38	32.64
10500.0	0.24	38.86	39.27
11000.0	0.30	35.59	41.08
11250.0	0.27	46.76	40.31
11500.0	0.29	32.67	37.99
12000.0	0.29	37.05	36.62
12500.0	0.32	44.11	51.44
13000.0	0.32	47.15	39.09
13500.0	0.33	37.14	34.28
14000.0	0.29	39.89	36.29
14500.0	0.36	38.08	41.11
15000.0	0.35	31.98	29.51
15500.0	0.32	31.08	29.43
16000.0	0.39	29.13	27.91
16500.0	0.48	33.10	51.69
17000.0	0.53	25.84	25.15
17500.0	0.50	23.36	22.87
18000.0	0.56	25.35	28.80