

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-FEMALE BULKHEAD RETURN LOSS (dB)	SMA-MALE RETURN LOSS (dB)
10	0.01	61.31	54.27
50	0.02	44.63	45.20
100	0.03	41.02	41.51
200	0.04	36.99	37.99
300	0.05	37.32	37.19
400	0.06	38.86	38.38
500	0.07	43.73	42.67
500	0.07	43.73	42.67
1000	0.09	46.00	41.41
1500	0.11	41.87	42.23
2000	0.13	34.52	36.95
2500	0.15	34.19	36.41
3500	0.17	40.21	37.99
4000	0.19	35.81	34.78
4500	0.20	35.88	35.53
5000	0.21	31.89	33.35
5500	0.22	32.03	34.67
6000	0.23	32.53	32.79
6500	0.24	37.74	38.82
7000	0.25	28.54	28.99
7500	0.27	26.16	26.74
8000	0.27	28.64	29.46
8500	0.27	34.45	35.96
9000	0.28	40.54	39.64
9500	0.29	31.92	32.28
10000	0.31	26.04	26.03
10500	0.31	28.65	29.00
11000	0.32	28.02	28.26
11500	0.32	44.30	47.49
12000	0.33	36.58	35.55
12500	0.34	30.66	29.90
13000	0.36	25.40	25.02
13500	0.36	32.27	31.57
14000	0.36	31.75	32.20
14500	0.37	54.49	46.67
15000	0.38	32.68	33.27
15500	0.39	27.77	27.82
16000	0.40	27.40	27.45
16500	0.41	26.15	26.79
17000	0.42	27.10	28.32
17500	0.42	46.93	61.17
18000	0.43	29.99	30.43