

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
100.0	0.07	45.2	46.6
200.0	0.08	44.7	43.2
300.0	0.09	45.7	42.6
400.0	0.09	50.1	44.0
500.0	0.10	57.6	48.4
600.0	0.11	54.6	51.4
700.0	0.12	53.4	48.9
800.0	0.12	59.9	45.6
900.0	0.13	56.5	44.9
1000.0	0.13	51.0	45.8
1100.0	0.14	50.3	48.5
1200.0	0.14	54.1	52.3
1300.0	0.15	57.9	49.3
1400.0	0.15	51.6	44.8
1500.0	0.15	45.1	41.7
1600.0	0.16	42.6	40.6
1700.0	0.17	42.4	41.2
1800.0	0.17	45.0	43.3
1900.0	0.17	54.3	47.3
2000.0	0.18	55.8	46.9
2400.0	0.19	41.5	39.0
3000.0	0.21	38.2	35.9
4000.0	0.25	36.9	35.6
5000.0	0.28	39.8	39.6
6000.0	0.32	29.3	28.3
7000.0	0.34	30.5	29.8
8000.0	0.37	32.4	31.8
9000.0	0.40	29.1	27.2
10000.0	0.42	29.9	29.3
11000.0	0.44	28.0	28.5
12000.0	0.45	33.1	36.3
13000.0	0.47	31.0	31.9
14000.0	0.49	29.1	30.8
15000.0	0.49	25.3	27.0
16000.0	0.58	23.4	23.7
17000.0	0.66	21.3	22.5
18000.0	0.62	23.2	29.5