

Armored Test Cable, N-Male/N-Male

APC-6FT-NMNM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
10.0	0.07	42.64	41.60
20.0	0.09	39.89	39.91
30.0	0.11	39.27	39.63
40.0	0.13	39.87	40.63
50.0	0.15	44.16	44.77
60.0	0.16	59.54	51.82
70.0	0.18	45.27	43.81
80.0	0.19	39.83	39.44
90.0	0.20	37.97	37.91
100.0	0.21	38.82	38.71
200.0	0.30	38.79	37.85
300.0	0.37	46.74	46.63
400.0	0.44	38.12	38.27
500.0	0.49	35.72	35.91
600.0	0.54	48.61	41.87
700.0	0.59	34.74	34.97
800.0	0.63	33.60	33.70
900.0	0.67	43.20	45.92
1000.0	0.71	36.07	36.14
1100.0	0.75	32.48	32.34
1500.0	0.88	34.65	34.41
2000.0	1.02	32.66	32.53
2500.0	1.16	35.20	34.42
3000.0	1.28	34.76	34.25
3500.0	1.39	34.69	34.37
4000.0	1.50	34.12	31.96
4500.0	1.61	37.94	37.65
5000.0	1.71	33.44	32.82
5500.0	1.81	35.72	36.85
6000.0	1.92	35.79	39.78
6500.0	2.01	28.33	28.68
7000.0	2.07	43.09	40.24
7500.0	2.17	24.79	25.77
8000.0	2.26	28.15	26.85
8500.0	2.36	26.44	28.20
9000.0	2.43	22.64	22.27
9500.0	2.45	29.54	27.95
10000.0	2.53	23.17	23.77
10500.0	2.52	23.43	20.94
11000.0	2.63	30.67	27.84
11500.0	2.72	24.50	23.32
12000.0	2.81	23.89	22.76
12500.0	2.87	35.66	27.74
13000.0	2.95	22.18	21.79
13500.0	2.99	21.47	21.55
14000.0	3.02	34.41	28.38
14500.0	3.03	23.44	22.52
15000.0	3.16	22.81	23.93
15500.0	3.28	32.30	29.55
16000.0	3.36	25.22	25.82
16500.0	3.43	28.48	27.42
17000.0	3.53	36.29	44.98
17500.0	3.60	38.80	32.39
18000.0	3.58	28.77	31.85

