

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	VSWR (:1)
10.0	64.84	162.19
55.0	52.36	301.74
100.0	47.86	361.27
150.0	45.79	404.03
200.0	45.17	327.48
250.0	45.75	318.39
300.0	47.47	206.14
350.0	50.50	156.54
400.0	55.72	113.05
470.0	70.01	76.30
530.0	59.64	53.17
570.0	58.08	41.36
630.0	64.47	27.45
670.0	48.08	20.04
730.0	26.32	10.08
770.0	12.70	3.91
830.0	4.10	1.56
870.0	2.91	1.13
900.0	2.39	1.23
930.0	2.07	1.36
950.0	1.91	1.41
980.0	1.72	1.41
1000.0	1.61	1.39
1050.0	1.38	1.32
1100.0	1.22	1.27
1150.0	1.10	1.25
1200.0	1.01	1.24
1250.0	0.94	1.24
1300.0	0.88	1.23
1350.0	0.84	1.22
1400.0	0.82	1.23
1450.0	0.81	1.27
1500.0	0.82	1.32
1550.0	0.84	1.38
1600.0	0.88	1.44
1650.0	0.93	1.50
1700.0	0.99	1.55
1750.0	1.05	1.57
1800.0	1.12	1.58
1850.0	1.20	1.56
1900.0	1.32	1.52
1970.0	1.64	1.42
2000.0	1.91	1.38
2050.0	2.83	1.36
2100.0	5.37	1.64
2150.0	11.53	2.73
2200.0	22.00	4.76
2250.0	27.28	6.98
2300.0	27.57	9.19
2350.0	31.52	11.59
2400.0	39.32	14.16
2450.0	33.30	16.74
2500.0	28.16	19.37
2550.0	25.35	21.82
2600.0	23.67	24.24
2650.0	22.63	26.34
2700.0	22.01	28.52
2750.0	21.72	30.26
2800.0	21.71	31.77
2850.0	22.02	33.10
2900.0	22.68	34.25
2950.0	23.86	34.82
3000.0	25.87	34.97