

Typical Performance Data

FREQUENCY	INSERTION LOSS	RETURN LOSS
(MHz)	(dB)	(dB)
0.3	71.17	0.01
3.0	50.95	0.00
10.0	40.60	0.00
30.0	31.75	0.02
100.0	26.72	0.09
300.0	33.29	0.18
1000.0	37.99	0.26
1200.0	36.53	0.28
1400.0	39.01	0.32
1500.0	46.28	0.35
1550.0	55.16	0.37
1600.0	41.84	0.40
1650.0	34.93	0.43
1700.0	30.04	0.47
1750.0	25.96	0.54
1800.0	22.30	0.63
1850.0	18.85	0.77
1900.0	15.52	1.01
2000.0	9.07	2.23
2100.0	3.91	6.85
2200.0	1.87	25.23
2220.0	1.74	33.92
2240.0	1.66	26.61
2260.0	1.60	22.70
2280.0	1.56	20.83
2300.0	1.52	20.04
2340.0	1.48	20.32
2380.0	1.47	20.85
2400.0	1.50	19.76
2430.0	1.58	16.64
2450.0	1.67	14.44
2470.0	1.80	12.46
2500.0	2.07	9.98
2600.0	3.60	4.89
2800.0	7.98	1.60
3000.0	11.96	0.82
3400.0	18.08	0.47
3500.0	19.37	0.45
3600.0	20.68	0.44
3800.0	23.21	0.43
4000.0	25.91	0.42
4100.0	27.34	0.42
4200.0	28.83	0.42
4300.0	30.45	0.43
4400.0	32.27	0.42
4600.0	36.88	0.43
4800.0	44.42	0.44
5000.0	50.16	0.45
5200.0	41.03	0.46
5400.0	37.12	0.48
5600.0	35.22	0.48
5800.0	34.66	0.50
6000.0	35.44	0.55
6200.0	32.93	0.70