

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	91.15	0.07
1000	71.61	0.24
5000	57.25	0.18
7000	54.49	0.05
10000	50.57	0.15
12000	47.13	0.11
14000	43.05	0.14
15000	41.06	0.16
18000	34.61	0.10
20000	30.17	0.25
21900	24.96	0.26
23000	22.01	0.20
25000	13.82	0.47
27000	3.89	3.56
29000	0.64	24.55
30000	0.68	17.25
31000	0.66	20.40
32000	0.64	27.00
33000	0.60	30.36
34000	0.51	27.22
35000	0.44	25.75
36000	0.49	27.16
37000	0.68	29.37
38000	0.85	27.93
39000	1.11	20.03
40000	2.19	12.72
42000	30.02	0.65
44000	21.72	0.36
46000	23.09	0.42
48000	24.80	0.48
50000	25.83	0.63
55000	24.86	1.55
60000	44.97	0.80
65000	38.46	1.86
67000	40.76	1.24