

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	VSWR (:1)
100	52.86	876.08
200	46.92	1074.59
300	43.57	564.53
400	41.36	384.59
500	39.78	235.50
600	38.68	162.13
700	37.99	122.93
800	37.67	97.57
1000	38.14	74.48
1200	40.48	67.51
1400	46.27	67.67
1600	61.67	71.57
1800	44.07	74.24
2000	38.83	71.53
2200	36.15	62.92
2400	35.37	51.16
2600	39.23	39.72
2670	39.23	39.72
2700	47.87	33.95
2800	31.69	27.49
2930	21.77	19.75
3000	13.37	10.68
3200	2.50	1.13
3400	1.74	1.44
3420	1.69	1.40
3440	1.64	1.35
3460	1.59	1.30
3480	1.56	1.26
3500	1.52	1.21
3520	1.50	1.17
3540	1.48	1.13
3560	1.47	1.09
3580	1.46	1.07
3600	1.45	1.05
3620	1.45	1.03
3640	1.45	1.02
3660	1.45	1.01
3680	1.46	1.02
3700	1.46	1.03
3720	1.48	1.06
3740	1.49	1.09
3760	1.51	1.13
3780	1.54	1.18
3800	1.57	1.23
3820	1.61	1.29
3840	1.65	1.35
3860	1.71	1.42
3880	1.77	1.49
3900	1.83	1.57
4000	2.20	1.86
4650	17.86	19.72
5000	30.61	27.97
5350	42.92	22.23
5500	53.98	18.04
6000	37.47	16.46
6500	37.68	26.52
7000	41.47	45.89
7500	51.17	67.14
8000	48.24	80.80
8500	40.31	120.90
9000	36.68	124.72
9500	35.26	233.79
9600	35.24	502.48
10000	34.84	165.77
10500	29.76	55.57
11000	25.28	93.97
11500	23.79	236.33
12000	27.47	138.85
12500	15.38	11.06
13000	13.31	14.68