

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	VSWR (:1)
10.0	77.28	508.40
100.0	57.45	289.52
500.0	44.18	127.06
1000.0	38.54	85.51
1500.0	35.72	69.90
2000.0	34.97	61.55
2500.0	39.92	55.73
3300.0	21.56	31.19
3700.0	11.62	14.08
4200.0	3.47	2.94
4300.0	2.66	2.29
4400.0	2.12	1.87
4500.0	1.74	1.61
4600.0	1.51	1.45
4700.0	1.35	1.35
4800.0	1.26	1.29
4900.0	1.19	1.27
5000.0	1.16	1.28
5100.0	1.14	1.29
5200.0	1.12	1.30
5300.0	1.12	1.32
5400.0	1.12	1.32
5500.0	1.13	1.31
5600.0	1.15	1.30
5700.0	1.18	1.26
5800.0	1.21	1.22
5900.0	1.26	1.14
6000.0	1.34	1.13
6500.0	2.44	1.89
7000.0	4.68	1.69
7500.0	26.25	10.20
8000.0	28.56	17.19
8500.0	29.27	21.47
9000.0	31.16	23.71
9500.0	33.11	22.45
10000.0	34.30	22.41
10500.0	35.18	21.11
11000.0	36.32	20.32
11500.0	36.98	22.65
12000.0	37.56	25.90