

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
100	0.14	40.8	40.0
1000	0.46	41.1	35.9
2000	0.63	36.3	48.3
3000	0.76	34.0	36.8
4000	0.88	32.2	32.8
5000	0.98	30.5	31.4
6000	1.07	29.5	29.7
7000	1.16	27.9	28.2
8000	1.24	25.6	26.2
9000	1.31	24.8	25.6
10000	1.38	25.0	25.1
11000	1.44	30.2	30.5
12000	1.51	33.0	36.2
13000	1.57	38.1	43.9
14000	1.63	29.8	35.8
15000	1.68	36.3	36.6
16000	1.75	28.6	29.8
17000	1.81	25.1	26.8
18000	1.88	24.1	25.8
19000	1.95	23.5	24.6
20000	2.01	21.6	22.2
21000	2.03	24.4	25.7
22000	2.08	24.8	26.9
23000	2.13	28.0	31.4
24000	2.22	29.2	36.1
25000	2.29	25.2	27.7
26000	2.35	23.2	25.4
27000	2.41	21.5	23.4
28000	2.46	21.6	22.8
29000	2.51	21.6	23.9
30000	2.53	24.6	27.7
31000	2.60	22.5	30.3
32000	2.63	28.4	33.4
33000	2.68	25.3	31.9
34000	2.74	22.5	24.7
35000	2.79	22.9	25.8
36000	2.85	21.0	22.6
37000	2.89	21.4	23.0
38000	2.95	20.9	22.7
39000	2.99	22.3	25.6
40000	3.04	21.4	27.1