

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.4mm-MALE 1 RETURN LOSS (dB)	2.4mm-MALE 2 RETURN LOSS (dB)
100	0.19	46.3	44.9
500	0.44	44.3	46.8
900	0.59	49.8	41.9
1000	0.62	54.2	48.7
4000	1.24	32.9	32.2
7000	1.66	35.0	34.5
10000	2.00	38.6	40.2
12000	2.20	35.4	36.5
14000	2.39	34.6	41.4
16000	2.58	31.4	29.6
18000	2.75	30.2	32.6
20000	2.92	41.4	35.5
21500	3.05	31.3	27.3
22500	3.13	29.8	29.8
23500	3.22	31.2	28.7
24500	3.29	31.8	31.2
25500	3.37	32.1	29.4
26500	3.45	37.2	41.9
27500	3.53	38.6	37.8
28500	3.61	30.8	26.4
30000	3.72	37.7	31.6
31000	3.79	33.8	31.3
32000	3.86	34.8	37.2
33000	3.94	42.0	41.3
34000	4.01	32.1	32.7
35000	4.08	30.7	38.9
36000	4.15	34.8	46.7
37000	4.23	33.2	34.1
38000	4.30	28.2	32.4
39000	4.37	27.4	28.0
40000	4.44	28.4	30.2
41000	4.50	41.3	29.9
42000	4.56	31.9	34.0
43000	4.63	35.3	38.0
44000	4.69	33.9	36.6
45000	4.76	39.3	36.4
46000	4.83	40.4	39.5
47000	4.90	53.8	47.4
48000	4.97	35.7	40.2
49000	5.04	30.6	35.2
50000	5.11	32.2	33.7