

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100	0.11	43.1	41.8
200	0.16	57.2	51.9
300	0.20	46.5	42.2
400	0.23	48.3	46.6
500	0.26	45.1	45.4
600	0.29	45.3	43.4
700	0.31	46.1	43.3
800	0.34	40.1	43.2
900	0.36	49.4	43.2
1000	0.39	38.3	38.8
1100	0.40	44.5	61.2
1250	0.43	50.3	48.1
1500	0.47	36.7	36.6
1750	0.52	40.6	43.5
2000	0.55	39.8	38.4
2001	0.55	39.8	38.4
2250	0.59	46.0	53.5
2500	0.62	37.5	38.4
2750	0.65	41.9	48.4
3000	0.69	34.8	37.1
3250	0.72	38.0	42.4
3500	0.75	31.5	32.5
3750	0.78	43.8	40.3
4000	0.80	30.5	30.9
4250	0.83	42.3	41.9
4500	0.87	33.0	34.4
5000	0.91	33.8	35.7
5500	0.96	33.7	35.3
6000	1.02	35.1	36.1
6500	1.06	34.4	33.5
7000	1.09	50.0	37.4
7500	1.15	48.9	37.1
8000	1.19	34.4	30.5
8500	1.22	33.7	30.0
9000	1.25	31.6	28.0
9500	1.30	29.0	25.9
10000	1.34	27.9	25.2
10500	1.36	29.2	28.4
11000	1.39	30.7	42.7
11500	1.43	35.9	34.6
12000	1.49	27.5	27.5
12500	1.53	27.5	27.0
13000	1.50	23.0	21.7
13500	1.59	27.7	24.7
14000	1.61	25.3	26.5
14500	1.62	28.2	27.7
15000	1.66	32.3	28.9
15500	1.68	31.4	42.2
16000	1.71	29.7	29.5
16500	1.74	25.6	26.1
17000	1.78	22.5	23.0
17500	1.85	25.5	25.0
18000	1.92	24.7	25.0