

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
10	0.01	56.42	53.61
50	0.03	47.74	48.10
100	0.05	42.79	43.15
200	0.07	36.69	37.16
300	0.09	33.35	33.83
400	0.11	31.71	32.13
500	0.12	31.27	31.59
600	0.13	32.06	32.21
700	0.14	34.32	34.30
800	0.15	38.57	39.00
900	0.15	40.26	45.22
1000	0.16	35.20	37.63
1500	0.20	31.38	30.96
2000	0.22	28.61	29.82
2500	0.24	34.38	50.13
3000	0.27	28.22	27.99
3500	0.28	28.39	29.87
4000	0.29	34.34	41.90
4500	0.32	27.03	26.95
5000	0.33	27.64	28.58
5500	0.33	35.01	37.07
6000	0.35	27.09	26.65
6500	0.37	25.91	26.22
7000	0.37	35.60	35.03
7500	0.39	26.41	25.94
8000	0.40	24.62	24.43
9000	0.42	25.40	24.91
10000	0.43	40.40	38.70
11000	0.47	23.41	23.55
12000	0.48	23.33	23.25
13000	0.48	39.58	38.95
14000	0.51	25.54	26.41
15000	0.53	23.06	24.22
16000	0.53	28.22	29.93
17000	0.55	31.93	35.40
18000	0.57	25.62	26.08
20000	0.59	39.62	35.61
22000	0.64	30.10	23.00
23000	0.64	40.64	26.22
24000	0.66	29.73	39.16
26500	0.71	27.26	25.34
28000	0.74	28.15	26.47
30000	0.78	23.77	41.03
32000	0.84	21.32	24.78
32000	0.84	21.32	24.78
34000	0.85	31.13	26.30
36000	0.89	20.70	21.98
38000	0.87	23.60	24.49
40000	0.87	30.82	19.34