

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	SSMP-FEMALE 1 RETURN LOSS (dB)	SSMP-FEMALE 2 RETURN LOSS (dB)
100	0.20	37.59	37.42
200	0.25	37.91	37.87
400	0.34	37.77	38.60
600	0.41	34.15	33.81
800	0.45	37.87	39.67
1000	0.50	30.36	30.14
2500	0.72	28.22	28.51
4000	0.88	31.74	32.54
5500	1.01	26.34	26.64
7000	1.16	19.94	20.11
8500	1.25	22.85	22.99
10000	1.31	43.44	43.27
11500	1.40	33.39	30.94
13000	1.49	25.87	24.01
14500	1.60	20.23	19.59
16000	1.63	37.13	33.98
17500	1.73	22.10	22.23
19000	1.78	31.24	29.75
20500	1.85	31.35	37.83
22000	1.93	25.13	30.43
23500	2.02	21.46	25.46
25000	2.08	22.04	25.18
26500	2.13	26.95	31.28
28000	2.19	32.85	44.58
29500	2.26	28.23	27.05
31000	2.35	23.65	21.39
32500	2.43	22.38	19.91
34000	2.48	23.54	20.81
35500	2.52	30.48	31.92
37000	2.64	18.74	19.50
38500	2.75	15.80	16.94
40000	2.74	19.88	25.92