

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
100	0.06	37.84	37.63
2000	0.32	38.66	38.09
3000	0.38	31.67	31.17
4000	0.45	25.72	25.89
5000	0.49	26.70	26.66
6000	0.53	31.94	31.93
7000	0.57	38.29	39.42
8000	0.60	38.76	38.88
9000	0.63	43.39	44.08
10000	0.66	30.51	30.92
11000	0.70	25.66	25.79
12000	0.73	27.33	27.47
13000	0.75	38.44	37.95
14000	0.79	25.51	25.68
15000	0.82	25.85	25.53
16000	0.83	39.24	34.02
17000	0.87	23.81	23.72
18000	0.90	24.51	23.96
19000	0.92	36.89	31.54
20000	0.97	21.45	21.25
21000	1.01	21.52	21.21
22000	1.00	33.29	31.10
23000	1.04	22.96	22.87
24000	1.10	20.02	19.85
25000	1.09	30.94	27.80
26000	1.13	23.19	23.27
27000	1.18	19.48	19.42
28000	1.18	24.98	24.25
29000	1.19	28.23	28.94
30000	1.24	20.72	20.63
31000	1.25	23.39	23.05
32000	1.25	32.20	30.93
33000	1.28	26.24	25.73
34000	1.31	25.38	25.32
35000	1.33	27.99	28.31
36000	1.34	33.40	33.62
37000	1.37	28.75	30.53
38000	1.39	27.01	29.06
39000	1.43	23.30	24.19
40000	1.45	21.32	21.69