

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SSMP-FEMALE 1 RETURN LOSS (dB)	SSMP-FEMALE 2 RETURN LOSS (dB)
100	0.10	37.57	37.62
200	0.14	36.01	35.94
300	0.17	38.57	38.40
400	0.20	44.84	45.53
500	0.22	52.80	50.94
600	0.24	40.49	39.81
700	0.25	37.03	36.38
800	0.27	36.14	35.53
900	0.28	37.14	36.83
1000	0.30	41.29	41.02
2000	0.39	38.06	37.78
3000	0.47	35.01	35.61
4000	0.53	32.77	32.66
5000	0.59	28.44	28.79
6000	0.64	43.54	57.12
7000	0.71	22.23	22.40
8000	0.74	25.77	26.02
9000	0.78	25.27	25.33
10000	0.83	23.78	24.05
11000	0.84	29.56	28.42
12000	0.87	34.69	32.02
13000	0.95	19.94	19.53
14000	0.95	24.50	23.50
15000	1.01	20.55	20.07
16000	1.02	23.75	23.21
17000	1.03	27.71	28.56
18000	1.06	27.47	26.33
19000	1.09	38.07	32.14
20000	1.13	29.85	26.51
21000	1.16	27.70	25.73
22000	1.19	31.05	32.35
23000	1.22	24.64	25.38
24000	1.25	29.22	34.00
25000	1.30	21.85	22.51
26000	1.30	33.37	43.65
27000	1.35	22.82	22.80
28000	1.36	25.71	25.27
29000	1.39	27.65	25.29
30000	1.47	19.98	19.18
31000	1.46	26.75	23.02
32000	1.57	18.27	17.02
33000	1.54	22.96	20.47
34000	1.62	18.56	17.08
35000	1.59	23.60	20.86
36000	1.66	19.55	17.67
37000	1.65	22.15	19.78
38000	1.70	21.23	18.37
39000	1.76	17.90	16.77
40000	1.71	30.61	23.55