

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.4mm-MALE 1 RETURN LOSS (dB)	2.4mm-MALE 2 RETURN LOSS (dB)
100	0.13	37.58	37.61
500	0.21	53.42	47.95
1000	0.29	31.31	32.63
2000	0.38	37.88	34.34
3000	0.43	31.14	33.15
4000	0.48	25.07	25.84
5000	0.52	26.41	26.49
6000	0.55	31.10	32.69
7000	0.58	36.01	37.32
8000	0.61	45.24	44.95
9000	0.64	40.69	45.08
10000	0.67	34.25	35.09
11000	0.69	38.85	38.89
12000	0.73	29.58	29.69
13000	0.76	25.33	25.41
14000	0.78	31.37	29.16
15000	0.80	34.96	34.29
16000	0.83	30.90	30.18
17000	0.86	34.55	34.95
18000	0.88	35.00	36.13
19000	0.91	49.40	56.70
20000	0.94	33.29	32.61
21000	0.97	33.15	31.71
22000	0.99	31.54	31.00
23000	1.02	42.89	34.79
24000	1.05	28.31	29.26
25000	1.07	31.33	30.40
26000	1.09	31.79	40.88
27000	1.12	28.89	29.13
28000	1.15	23.97	24.68
29000	1.17	30.24	30.80
30000	1.20	30.64	31.27
31000	1.24	22.63	22.28
32000	1.25	26.30	26.56
33000	1.26	35.52	33.61
34000	1.30	23.83	24.29
35000	1.32	25.28	24.98
36000	1.33	37.57	32.17
37000	1.36	25.45	24.58
38000	1.36	39.13	33.22
39000	1.39	31.57	33.19
40000	1.41	33.74	45.54
41000	1.44	27.84	33.76
42000	1.45	39.45	46.22
43000	1.49	25.05	26.75
44000	1.49	27.00	29.60
45000	1.52	27.91	29.90
46000	1.54	34.03	38.69
47000	1.58	24.02	23.05
48000	1.61	23.51	22.40
49000	1.61	30.74	25.48
50000	1.70	21.77	21.05