

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMP-FEMALE RETURN LOSS (dB)	2.92mm-MALE RETURN LOSS (dB)
100	0.07	38.25	39.07
200	0.10	34.65	35.56
400	0.15	43.59	48.70
600	0.19	32.98	35.66
800	0.21	40.49	39.13
1000	0.24	32.20	37.73
2000	0.34	32.04	32.30
3000	0.41	39.62	30.09
4000	0.46	32.17	31.54
5000	0.52	27.50	46.80
6000	0.57	27.34	31.39
7000	0.62	32.23	27.99
8000	0.65	40.79	29.62
9000	0.69	29.55	29.85
10000	0.74	27.35	27.20
11000	0.77	29.05	26.94
12000	0.80	31.34	31.22
13000	0.83	32.05	45.60
14000	0.87	36.47	28.28
15000	0.91	34.17	24.93
16000	0.94	28.38	25.06
17000	0.96	27.16	28.47
18000	0.99	30.69	33.29
19000	1.02	29.02	29.24
20000	1.05	26.24	28.07
21000	1.09	24.95	30.08
22000	1.12	25.40	27.58
23000	1.15	27.60	22.21
24000	1.16	26.31	21.49
25000	1.19	24.14	24.22
26000	1.22	23.52	29.89
27000	1.25	24.06	27.46
28000	1.28	24.92	26.64
29000	1.31	26.92	32.15
30000	1.35	23.08	36.85
31000	1.41	20.97	28.09
32000	1.44	19.81	24.16
33000	1.46	20.39	21.04
34000	1.50	20.00	22.55