

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	Mini SMP-FEMALE RETURN LOSS (dB)	SMP-FEMALE RETURN LOSS (dB)
100	0.08	37.65	40.28
200	0.12	34.59	37.15
300	0.14	38.74	41.26
400	0.17	42.59	43.12
500	0.19	34.12	36.40
600	0.20	33.27	35.80
700	0.22	39.24	42.11
800	0.23	39.23	40.33
900	0.25	32.71	34.78
1000	0.26	33.65	36.24
2000	0.36	31.40	32.87
3000	0.43	32.41	31.66
4000	0.50	34.83	30.33
5000	0.55	39.70	30.59
6000	0.60	38.18	32.71
7000	0.65	36.04	35.59
8000	0.69	37.79	39.91
9000	0.74	36.96	41.81
10000	0.78	38.18	33.24
11000	0.82	39.44	28.92
12000	0.86	42.03	27.30
13000	0.89	39.69	27.53
14000	0.93	35.26	27.41
15000	0.97	33.48	26.67
16000	1.00	27.73	25.89
17000	1.04	24.57	25.45
18000	1.07	24.96	25.13
19000	1.11	25.41	22.82
20000	1.12	35.58	24.42
21000	1.13	31.52	27.63
22000	1.15	29.62	24.34
23000	1.17	30.94	21.12
24000	1.17	32.62	21.83
25000	1.19	24.72	26.71
26000	1.24	20.48	35.07
27000	1.32	19.48	22.46
28000	1.38	22.44	20.40
29000	1.39	29.67	23.60
30000	1.41	22.80	33.28
31000	1.46	18.82	22.64
32000	1.48	19.31	20.66
33000	1.45	21.10	19.94
34000	1.22	21.85	19.19