

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.4mm-MALE 1 RETURN LOSS (dB)	2.4mm-MALE 2 RETURN LOSS (dB)
100	0.10	42.79	41.05
200	0.12	41.26	40.51
300	0.14	40.36	40.45
400	0.16	42.59	42.12
500	0.18	42.22	48.30
600	0.20	41.34	42.18
700	0.21	41.33	40.26
800	0.23	40.80	41.02
900	0.24	44.81	48.62
1000	0.25	42.78	40.98
2000	0.35	43.63	49.09
4000	0.49	33.21	33.71
6000	0.59	29.49	31.34
8000	0.66	33.44	35.33
10000	0.75	24.29	24.13
12000	0.80	46.06	34.27
14000	0.88	23.01	22.85
16000	0.94	23.08	22.98
18000	0.98	25.88	25.00
20000	1.08	21.12	20.80
22000	1.11	32.00	29.55
24000	1.18	28.32	30.43
26000	1.24	35.85	38.22
28000	1.31	38.82	34.22
30000	1.38	35.39	36.56
32000	1.43	25.76	25.90
34000	1.48	33.06	30.56
36000	1.57	22.54	22.17
38000	1.60	30.20	29.87
40000	1.64	27.63	28.53
42000	1.71	33.47	30.53
44000	1.77	34.28	29.08
46000	1.82	38.20	31.39
48000	1.90	33.38	32.35
50000	1.96	21.50	21.78