

Test Cable, SMA-Male/SMA-Male

FLC-1M-SMSM+

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 VSWR (:1)	SMA-MALE 2 VSWR (:1)
0.1	0.17	1.02	1.02
0.5	0.32	1.04	1.03
1.0	0.44	1.06	1.05
1.5	0.55	1.07	1.06
2.0	0.64	1.07	1.05
2.5	0.73	1.08	1.06
3.0	0.80	1.07	1.05
3.5	0.86	1.05	1.04
4.0	0.91	1.03	1.03
4.5	0.96	1.02	1.02
5.0	1.02	1.02	1.02
5.5	1.07	1.04	1.04
6.0	1.11	1.05	1.05
6.5	1.16	1.08	1.06
7.0	1.22	1.10	1.09
7.5	1.27	1.11	1.09
8.0	1.28	1.11	1.09
8.5	1.31	1.12	1.11
9.0	1.36	1.12	1.10
9.5	1.38	1.12	1.10
10.0	1.39	1.11	1.12
10.5	1.44	1.11	1.11
11.0	1.51	1.10	1.10
11.5	1.49	1.10	1.11
12.0	1.51	1.10	1.09
12.5	1.60	1.08	1.08
13.0	1.64	1.07	1.08
13.5	1.67	1.08	1.07
14.0	1.75	1.06	1.07
14.5	1.86	1.08	1.07
15.0	1.85	1.11	1.09
15.5	1.87	1.10	1.09
16.0	1.98	1.11	1.11
16.5	2.01	1.14	1.15
17.0	1.96	1.12	1.15
17.5	2.07	1.14	1.16
18.0	2.18	1.16	1.17
18.5	2.15	1.15	1.14
19.0	2.18	1.16	1.15
19.5	2.22	1.18	1.15
20.0	2.25	1.18	1.15
20.5	2.25	1.18	1.12
21.0	2.17	1.18	1.13
21.5	2.22	1.19	1.16
22.0	2.31	1.17	1.13
22.5	2.32	1.16	1.13
23.0	2.33	1.16	1.14
23.5	2.44	1.17	1.09
24.0	2.57	1.16	1.10
24.5	2.50	1.19	1.11
25.0	2.47	1.16	1.13
25.5	2.52	1.16	1.14
26.0	2.59	1.23	1.22

