

# Test Cable, SMA-Male/SMA-Male

# FLC-2FT-SMSM+

## Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 VSWR (:1)	SMA-MALE 2 VSWR (:1)
0.1	0.09	1.02	1.02
0.5	0.18	1.03	1.03
1.0	0.26	1.05	1.05
1.5	0.33	1.07	1.07
2.0	0.38	1.08	1.08
2.5	0.43	1.07	1.08
3.0	0.48	1.08	1.07
3.5	0.51	1.07	1.06
4.0	0.55	1.05	1.05
4.5	0.57	1.04	1.03
5.0	0.60	1.03	1.02
5.5	0.64	1.04	1.03
6.0	0.67	1.05	1.05
6.5	0.69	1.06	1.07
7.0	0.73	1.08	1.11
7.5	0.76	1.10	1.14
8.0	0.79	1.13	1.15
8.5	0.80	1.15	1.15
9.0	0.83	1.17	1.17
9.5	0.83	1.18	1.19
10.0	0.78	1.19	1.19
10.5	0.82	1.18	1.17
11.0	0.87	1.18	1.16
11.5	0.84	1.16	1.16
12.0	0.88	1.14	1.16
12.5	0.96	1.13	1.15
13.0	0.99	1.15	1.12
13.5	1.00	1.15	1.12
14.0	0.99	1.15	1.13
14.5	1.07	1.16	1.12
15.0	1.09	1.18	1.10
15.5	1.06	1.18	1.12
16.0	1.14	1.18	1.14
16.5	1.18	1.20	1.16
17.0	1.13	1.21	1.15
17.5	1.18	1.19	1.18
18.0	1.30	1.21	1.23
18.5	1.29	1.25	1.25
19.0	1.36	1.29	1.25
19.5	1.41	1.31	1.25
20.0	1.43	1.31	1.28
20.5	1.42	1.30	1.31
21.0	1.33	1.29	1.34
21.5	1.31	1.24	1.29
22.0	1.33	1.28	1.29
22.5	1.30	1.31	1.30
23.0	1.28	1.32	1.29
23.5	1.44	1.32	1.26
24.0	1.46	1.29	1.24
24.5	1.36	1.27	1.21
25.0	1.36	1.22	1.23
25.5	1.45	1.22	1.17
26.0	1.51	1.14	1.13

