

Test Cable, SMA-Male/SMA-Male

FLC-2M-SMSM+

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 VSWR (:1)	SMA-MALE 2 VSWR (:1)
0.1	0.27	1.01	1.01
0.5	0.54	1.02	1.02
1.0	0.79	1.03	1.03
1.5	0.99	1.05	1.04
2.0	1.16	1.06	1.05
2.5	1.31	1.06	1.05
3.0	1.44	1.05	1.04
3.5	1.57	1.04	1.04
4.0	1.68	1.03	1.03
4.5	1.80	1.02	1.02
5.0	1.90	1.02	1.02
5.5	2.01	1.04	1.03
6.0	2.11	1.05	1.05
6.5	2.21	1.06	1.06
7.0	2.31	1.07	1.07
7.5	2.41	1.08	1.08
8.0	2.50	1.08	1.10
8.5	2.59	1.09	1.10
9.0	2.67	1.09	1.10
9.5	2.75	1.09	1.10
10.0	2.83	1.09	1.09
10.5	2.91	1.09	1.10
11.0	2.99	1.09	1.09
11.5	3.07	1.10	1.09
12.0	3.15	1.09	1.09
12.5	3.22	1.09	1.08
13.0	3.29	1.08	1.07
13.5	3.37	1.07	1.05
14.0	3.45	1.07	1.06
14.5	3.53	1.07	1.07
15.0	3.63	1.06	1.09
15.5	3.71	1.10	1.11
16.0	3.79	1.11	1.13
16.5	3.88	1.14	1.14
17.0	3.96	1.16	1.16
17.5	4.06	1.19	1.18
18.0	4.14	1.20	1.16
18.5	4.24	1.22	1.19
19.0	4.30	1.21	1.17
19.5	4.38	1.23	1.17
20.0	4.42	1.22	1.16
20.5	4.47	1.19	1.13
21.0	4.52	1.20	1.11
21.5	4.57	1.16	1.10
22.0	4.63	1.15	1.09
22.5	4.69	1.12	1.06
23.0	4.76	1.10	1.03
23.5	4.82	1.06	1.05
24.0	4.89	1.04	1.07
24.5	4.93	1.05	1.10
25.0	5.02	1.04	1.12
25.5	5.10	1.07	1.14
26.0	5.19	1.09	1.18

