

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	2.92mm-FEMALE 1 VSWR (:1)	2.92mm-FEMALE 2 VSWR (:1)
0.01	0.04	1.01	1.01
0.05	0.01	1.00	1.00
0.10	0.02	1.01	1.00
0.20	0.02	1.01	1.00
0.30	0.02	1.01	1.00
0.40	0.02	1.01	1.01
0.50	0.03	1.01	1.01
0.60	0.02	1.01	1.01
0.70	0.03	1.01	1.01
0.80	0.03	1.01	1.01
0.90	0.03	1.01	1.01
1.00	0.03	1.01	1.01
2.00	0.03	1.00	1.01
3.00	0.04	1.01	1.01
4.00	0.04	1.01	1.02
5.00	0.05	1.02	1.02
6.00	0.05	1.02	1.02
7.00	0.05	1.03	1.03
8.00	0.06	1.04	1.04
9.00	0.06	1.05	1.05
10.00	0.06	1.05	1.05
11.00	0.07	1.06	1.06
12.00	0.07	1.07	1.07
13.00	0.07	1.06	1.07
14.00	0.08	1.06	1.07
15.00	0.08	1.06	1.06
16.00	0.08	1.05	1.06
17.00	0.08	1.04	1.05
18.00	0.08	1.04	1.04
19.00	0.09	1.04	1.04
20.00	0.09	1.04	1.04
21.00	0.11	1.05	1.05
22.00	0.13	1.06	1.06
23.00	0.13	1.06	1.07
24.00	0.09	1.08	1.07
25.00	0.08	1.08	1.07
26.00	0.09	1.08	1.08
27.00	0.10	1.08	1.09
28.00	0.10	1.08	1.08
29.00	0.11	1.08	1.09
30.00	0.12	1.08	1.08
31.00	0.12	1.07	1.09
32.00	0.12	1.06	1.08
33.00	0.13	1.05	1.07
34.00	0.12	1.05	1.06
35.00	0.13	1.04	1.05
36.00	0.13	1.03	1.04
37.00	0.13	1.02	1.03
38.00	0.13	1.02	1.03
39.00	0.14	1.02	1.03
40.00	0.15	1.03	1.02