

Right Angle Adapter, N-Female to N-Male **NF-NMR50+**

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-FEMALE VSWR (:1)	N-MALE VSWR (:1)
10	0.003	1.00	1.00
20	0.004	1.00	1.00
30	0.007	1.00	1.00
40	0.008	1.00	1.00
50	0.009	1.00	1.00
60	0.010	1.01	1.00
70	0.012	1.01	1.01
80	0.014	1.01	1.01
90	0.015	1.01	1.01
100	0.017	1.01	1.01
150	0.023	1.01	1.01
200	0.027	1.01	1.01
350	0.033	1.01	1.01
300	0.032	1.01	1.01
350	0.033	1.01	1.01
400	0.035	1.01	1.01
450	0.036	1.01	1.01
500	0.038	1.01	1.01
550	0.038	1.01	1.01
600	0.041	1.01	1.01
700	0.042	1.02	1.01
800	0.043	1.02	1.01
900	0.045	1.02	1.01
1000	0.047	1.02	1.01
1100	0.047	1.02	1.01
1200	0.049	1.01	1.01
1400	0.052	1.01	1.01
1600	0.052	1.01	1.01
1800	0.053	1.01	1.01
2000	0.054	1.01	1.01
2200	0.057	1.01	1.01
2400	0.058	1.01	1.01
2600	0.059	1.01	1.01
2800	0.058	1.01	1.01
3000	0.062	1.01	1.01
3200	0.063	1.00	1.00
3400	0.063	1.00	1.00
3600	0.062	1.01	1.01
3800	0.066	1.01	1.01
4000	0.068	1.02	1.02
4200	0.070	1.02	1.02
4400	0.061	1.02	1.03
4600	0.054	1.02	1.03
4800	0.057	1.02	1.03
5000	0.063	1.02	1.04
5200	0.087	1.02	1.04
5400	0.081	1.02	1.04
5600	0.090	1.02	1.04
5800	0.068	1.02	1.04
6000	0.067	1.01	1.04