

Right Angle Adapter, N-Female to N-Male

NF-NMR50-18+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-FEMALE VSWR (:1)	N-MALE VSWR (:1)
10	0.003	1.00	1.00
20	0.004	1.00	1.00
30	0.007	1.00	1.00
40	0.008	1.00	1.00
50	0.009	1.00	1.00
60	0.010	1.01	1.00
70	0.012	1.01	1.01
80	0.014	1.01	1.01
90	0.015	1.01	1.01
100	0.017	1.01	1.01
100	0.017	1.01	1.01
150	0.023	1.01	1.01
200	0.027	1.01	1.01
250	0.029	1.01	1.01
300	0.032	1.01	1.01
350	0.033	1.01	1.01
400	0.035	1.01	1.01
450	0.036	1.01	1.01
500	0.038	1.01	1.01
550	0.038	1.01	1.01
600	0.041	1.01	1.01
650	0.041	1.02	1.01
700	0.042	1.02	1.01
750	0.042	1.02	1.01
800	0.043	1.02	1.01
900	0.045	1.02	1.01
1000	0.047	1.02	1.01
1200	0.049	1.01	1.01
1400	0.052	1.01	1.01
1600	0.052	1.01	1.01
1800	0.053	1.01	1.01
2000	0.054	1.01	1.01
2500	0.055	1.01	1.01
3000	0.062	1.01	1.01
3500	0.063	1.00	1.01
4000	0.068	1.02	1.02
5000	0.063	1.02	1.04
6000	0.067	1.01	1.04
7000	0.071	1.02	1.03
8000	0.087	1.02	1.04
9000	0.101	1.04	1.05
10000	0.112	1.02	1.03
11000	0.093	1.05	1.03
12000	0.044	1.06	1.10
13000	0.111	1.06	1.07
14000	0.159	1.08	1.09
15000	0.116	1.12	1.12
16000	0.038	1.02	1.15
17000	0.193	1.10	1.16
18000	0.131	1.16	1.23

