

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.4mm-FEMALE RETURN LOSS (dB)	2.4mm-MALE RETURN LOSS (dB)
100	0.09	39.2	40.1
400	0.20	39.6	40.8
700	0.26	43.7	47.8
1000	0.31	44.8	48.6
1500	0.37	37.7	46.3
2000	0.42	37.3	37.9
2500	0.47	38.8	37.1
3000	0.52	39.3	61.4
3500	0.56	32.2	34.0
4000	0.60	30.9	32.1
4500	0.63	43.9	46.2
5000	0.67	31.9	31.2
5500	0.70	30.5	31.3
6000	0.73	31.2	32.3
6500	0.76	35.7	37.7
7000	0.79	27.6	28.0
7500	0.82	27.5	27.3
8000	0.84	34.9	38.8
9000	0.89	26.3	27.0
10000	0.93	38.8	35.3
11000	0.98	29.0	28.5
12000	1.01	32.5	32.0
13000	1.05	32.7	30.9
14000	1.10	28.7	27.6
15000	1.13	43.8	37.1
16000	1.17	33.5	31.9
17000	1.21	29.5	30.3
18000	1.25	28.6	29.8
20000	1.32	26.2	29.7
22000	1.39	26.5	33.7
24000	1.47	27.7	32.9
26000	1.54	24.8	25.6
28000	1.61	25.0	24.4
30000	1.66	26.3	25.4
32000	1.73	29.2	31.7
34000	1.79	28.4	35.3
36000	1.86	26.4	27.7
38000	1.91	28.9	29.7
40000	1.97	32.7	38.7
45000	2.12	34.3	29.6
50000	2.28	32.0	45.4