

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.4mm-MALE 1 RETURN LOSS (dB)	2.4mm-MALE 2 RETURN LOSS (dB)
50	0.06	31.01	30.98
100	0.09	29.22	29.09
400	0.21	35.14	35.57
700	0.28	33.24	34.09
1000	0.33	31.59	31.99
1500	0.40	37.37	38.47
2000	0.46	41.88	41.71
2500	0.52	38.74	36.09
3000	0.57	41.22	41.18
3500	0.61	45.29	50.05
4000	0.66	57.25	40.13
4500	0.70	37.59	34.42
5000	0.73	46.83	40.10
5500	0.78	35.09	33.06
6000	0.81	29.06	29.36
6500	0.84	35.75	32.23
7000	0.88	36.75	33.44
7500	0.91	31.83	32.15
8000	0.94	29.38	28.04
9000	0.99	38.52	36.67
10000	1.04	29.48	29.74
11000	1.09	37.64	41.24
12000	1.14	28.14	29.23
13000	1.18	38.25	34.64
14000	1.23	29.99	28.64
15000	1.27	29.78	29.36
16000	1.31	30.21	31.02
17000	1.35	28.58	27.95
18000	1.39	36.08	47.29
20000	1.51	20.56	20.92
22000	1.60	21.36	21.47
24000	1.66	23.10	21.84
26000	1.72	29.39	25.34
28000	1.80	22.26	22.23
30000	1.84	29.80	30.74
32000	1.92	34.07	36.61
34000	2.04	20.14	20.46
36000	2.09	22.60	22.84
38000	2.17	21.35	20.08
40000	2.26	21.50	20.22
45000	2.37	27.83	40.26
50000	2.80	21.24	19.24