

*Typical Performance Data*

FREQ	INSERTION LOSS RF & DC-RF with current	ISOLATION RF & DC-DC 0 mA	VSWR RF & DC with current
(MHz)	(dB)	(dB)	(:1)
10	0.17	36.31	1.25
20	0.09	48.08	1.10
30	0.07	54.91	1.07
40	0.06	59.52	1.05
50	0.05	63.10	1.04
60	0.05	65.57	1.04
70	0.04	67.27	1.03
80	0.05	68.61	1.03
90	0.04	69.03	1.03
100	0.04	69.24	1.03
150	0.04	68.46	1.02
200	0.05	66.77	1.02
250	0.05	64.79	1.02
300	0.05	63.82	1.01
350	0.05	62.36	1.01
400	0.05	61.18	1.01
450	0.06	60.23	1.01
500	0.06	59.14	1.01
550	0.08	58.59	1.01
600	0.07	57.69	1.01
650	0.07	57.25	1.01
700	0.08	56.29	1.01
750	0.09	55.66	1.01
800	0.11	55.02	1.01
850	0.10	54.61	1.02
900	0.09	54.09	1.01
950	0.09	53.65	1.02
1000	0.09	52.98	1.02
1500	0.09	46.74	1.04
2000	0.11	42.79	1.09
2500	0.10	39.96	1.12
3000	0.10	36.36	1.16
3500	0.10	33.45	1.17
4000	0.12	31.23	1.16
4500	0.14	30.08	1.11
5000	0.17	29.13	1.06
5500	0.20	28.12	1.01
6000	0.23	27.37	1.03
6500	0.28	25.81	1.03
7000	0.36	23.78	1.07
7500	0.35	22.65	1.09
8000	0.28	22.78	1.11
8500	0.20	23.56	1.11
9000	0.14	23.77	1.11
9500	0.18	23.86	1.13
10000	0.26	23.54	1.20
10500	0.40	23.50	1.23
11000	0.56	22.82	1.31
11500	0.70	21.81	1.37
12000	0.75	20.82	1.36
12500	0.76	19.68	1.37
13000	0.91	15.85	1.37