

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
100	0.22	47.0	40.8
1000	0.70	45.5	35.5
2000	0.97	37.5	41.6
3000	1.18	46.4	48.9
4000	1.37	34.1	34.6
5000	1.53	30.6	29.7
6000	1.67	33.0	34.1
7000	1.81	32.9	31.6
8000	1.93	30.7	30.3
9000	2.05	32.7	33.2
10000	2.16	35.7	35.9
11000	2.28	26.1	26.9
12000	2.36	36.2	34.6
13000	2.46	33.0	33.7
14000	2.55	39.6	36.6
15000	2.65	30.5	37.3
16000	2.74	51.2	34.8
17000	2.83	29.8	30.9
18000	2.91	41.4	36.5
19000	3.00	33.1	30.9
20000	3.08	30.1	31.5
21000	3.16	31.3	33.5
22000	3.24	37.8	31.1
23000	3.36	24.2	23.1
24000	3.41	25.4	25.4
25000	3.47	31.6	36.1
26500	3.60	24.5	25.7
28000	3.69	30.8	33.4
29000	3.77	27.7	30.8
30000	3.83	27.1	32.7
31000	3.91	25.5	25.1
32000	3.98	26.1	30.6
33000	4.04	24.3	29.4
34000	4.11	26.8	29.6
35000	4.20	20.3	21.6
36000	4.23	23.9	32.3
37000	4.30	25.4	27.8
38000	4.36	23.3	24.2
39000	4.42	23.3	22.1
40000	4.44	31.8	36.1