

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
0.01	0.16	29.13	29.18
0.10	0.51	54.28	50.06
0.20	0.72	43.93	46.08
0.30	0.89	39.63	40.91
0.40	1.03	39.93	39.75
0.50	1.16	36.64	37.09
0.60	1.28	29.04	29.06
0.70	1.39	30.77	31.02
0.80	1.49	26.76	27.14
0.90	1.58	30.39	31.83
1.00	1.68	27.91	28.13
2.00	2.43	25.17	25.39
3.00	3.03	23.12	23.38
4.00	3.55	21.57	21.76
5.00	4.00	22.71	23.51
6.00	4.41	24.88	25.94
7.00	4.81	24.13	23.52
7.50	4.99	28.22	30.71
8.00	5.19	26.76	25.42
8.50	5.36	26.12	26.56
9.00	5.54	26.25	26.42
9.50	5.72	24.32	25.64
10.00	5.89	26.01	31.08
10.50	6.07	23.70	25.04
11.00	6.22	26.44	25.20
11.50	6.37	24.98	27.98
12.00	6.54	25.02	25.52
12.50	6.70	23.83	24.62
13.00	6.85	27.02	27.73
13.50	7.01	23.78	26.31
14.00	7.16	25.50	30.03
14.50	7.33	23.70	23.76
15.00	7.47	24.77	31.37
15.50	7.62	24.36	24.22
16.00	7.76	25.33	28.42
16.50	7.93	23.15	23.69
17.00	8.06	24.60	25.30
17.50	8.22	22.53	23.01
18.00	8.35	23.72	24.97