

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	N-MALE RETURN LOSS (dB)	SMA-MALE RETURN LOSS (dB)
0.01	0.03	45.28	44.29
0.1	0.11	35.16	35.11
0.2	0.15	37.76	37.51
0.4	0.22	33.95	33.68
0.6	0.27	33.97	33.38
0.8	0.31	38.07	37.35
1.0	0.34	45.14	43.21
1.5	0.43	30.41	30.10
2.0	0.50	26.01	25.62
2.5	0.56	26.59	26.10
3.0	0.61	38.05	35.37
3.5	0.66	34.29	34.35
4.0	0.72	27.38	26.93
4.5	0.77	25.06	24.47
5.0	0.80	32.93	30.47
5.5	0.84	38.85	35.14
6.0	0.88	32.90	32.53
6.5	0.93	30.72	29.52
7.0	0.96	37.30	32.27
7.5	1.00	33.66	34.04
8.0	1.05	26.42	28.41
8.5	1.08	24.60	25.87
9.0	1.12	29.34	28.82
9.5	1.15	45.62	35.21
10.0	1.19	26.53	28.87
10.5	1.24	22.72	23.83
11.0	1.27	22.91	23.09
11.5	1.29	28.74	26.45
12.0	1.32	41.31	29.22
12.5	1.36	26.07	22.91
13.0	1.40	23.82	20.63
13.5	1.42	26.98	22.46
14.0	1.44	40.89	31.10
14.5	1.49	27.92	24.22
15.0	1.53	24.55	19.46
15.5	1.56	24.74	19.04
16.0	1.57	30.05	23.38
16.5	1.60	27.47	32.16
17.0	1.66	21.37	21.43
17.5	1.70	20.27	18.58
18.0	1.70	23.26	20.34