

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
0.01	0.05	40.07	38.81
0.1	0.14	53.03	46.22
0.2	0.21	46.52	48.41
0.4	0.32	34.36	34.49
0.6	0.40	28.83	28.87
0.8	0.46	34.80	34.81
1.0	0.51	31.22	31.58
1.5	0.62	44.56	47.68
2.0	0.73	26.61	27.11
2.5	0.83	22.84	23.27
3.0	0.91	23.14	23.37
3.5	0.97	28.01	27.68
4.0	1.03	33.05	35.77
4.5	1.10	36.24	33.73
5.0	1.16	38.12	50.29
5.5	1.23	37.32	46.67
6.0	1.29	41.87	37.74
6.5	1.36	32.58	30.88
7.0	1.42	33.47	31.17
7.5	1.47	41.59	30.81
8.0	1.53	39.74	28.83
8.5	1.58	28.54	25.92
9.0	1.63	25.95	25.14
9.5	1.68	28.72	26.51
10.0	1.72	45.94	28.16
10.5	1.78	28.84	25.75
11.0	1.84	25.94	25.17
11.5	1.89	27.82	27.40
12.0	1.93	41.20	31.36
12.5	1.96	31.81	27.85
13.0	2.01	26.27	25.49
13.5	2.08	24.45	23.90
14.0	2.13	29.51	26.25
14.5	2.18	30.97	27.93
15.0	2.23	25.96	26.71
15.5	2.29	24.46	23.36
16.0	2.34	25.13	21.78
16.5	2.38	25.67	21.67
17.0	2.42	26.82	21.83
17.5	2.46	27.35	20.99
18.0	2.51	24.70	20.35

