

## Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
0.01	0.06	36.67	35.95
0.04	0.13	31.60	31.87
0.07	0.17	40.15	41.06
0.10	0.20	36.31	36.14
0.12	0.23	32.76	32.97
0.38	0.41	31.51	31.49
0.65	0.54	30.69	30.46
0.92	0.65	30.69	30.24
1.19	0.72	32.36	32.60
1.46	0.81	36.46	35.10
1.73	0.89	46.95	36.51
2.00	0.96	38.59	35.54
2.02	0.99	23.87	23.71
2.81	1.16	26.62	26.35
3.61	1.33	25.09	25.50
4.40	1.47	29.18	31.87
5.20	1.60	28.39	31.22
6.00	1.73	29.22	33.53
6.02	1.74	26.62	27.80
6.76	1.85	27.90	28.24
7.51	1.96	30.84	32.14
8.26	2.07	27.12	26.74
9.01	2.18	27.09	27.39
9.75	2.28	24.44	24.15
10.50	2.38	28.03	31.75
11.25	2.49	23.40	23.11
12.00	2.57	29.96	34.25
12.02	2.59	24.86	25.70
12.76	2.68	24.92	25.89
13.51	2.76	30.02	39.11
14.26	2.86	27.26	28.03
15.01	2.94	39.21	43.70
15.75	3.04	28.33	27.12
16.50	3.11	34.32	28.60
17.25	3.22	25.31	22.97
18.00	3.29	30.55	26.01