

# Coaxial Band Pass Filter

# VBF-2555+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
50	72.26	0.06
200	74.05	0.15
500	59.32	0.25
1000	48.65	0.32
1970	37.58	0.75
2000	36.10	0.81
2200	20.97	1.87
2300	10.44	5.56
2350	6.26	11.95
2500	3.77	15.73
2555	3.69	16.59
2610	3.78	13.93
2850	7.92	12.33
2920	14.90	5.12
3000	24.49	2.63
3200	37.30	1.23
3250	38.25	1.14
3700	46.50	0.76
4500	34.74	0.56
5500	27.76	0.45

REV. X1  
VBF-2555+  
080221  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

