

Coaxial Band Pass Filter

VBF-4440+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
50	75.21	0.01
500	67.47	0.02
1000	44.89	0.02
2000	23.83	0.18
2300	19.02	0.32
2900	9.98	0.94
3300	4.99	2.70
3700	1.99	7.09
4200	0.88	18.20
4440	0.84	24.41
4700	0.94	19.22
5000	1.36	11.74
5400	3.89	4.30
5650	7.53	1.97
6000	14.41	0.80
6650	31.12	0.39
6750	35.25	0.40
9000	26.00	0.41
12000	34.49	0.33

REV. X1
VBF-4440+
080221
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

