

*Typical Performance Data*

FREQUENCY (GHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
60.0	97.28	0.09
60.6	85.81	0.07
61.2	104.74	0.05
61.8	114.48	0.04
62.4	107.83	0.12
63.0	102.50	0.08
63.6	100.44	0.18
64.2	108.55	0.12
64.8	101.89	0.13
65.4	95.83	0.11
66.0	104.02	0.12
66.6	104.95	0.09
67.2	108.23	0.09
67.8	107.14	0.11
68.4	105.59	0.08
69.0	106.11	0.09
69.6	100.93	0.09
70.2	102.63	0.10
70.8	93.66	0.12
71.4	100.48	0.12
72.0	81.30	0.15
72.6	74.98	0.17
73.2	65.20	0.16
73.8	54.38	0.20
74.4	40.98	0.25
75.0	23.30	0.48
75.6	1.52	17.18
76.2	0.79	16.94
76.8	0.66	18.22
77.4	0.65	14.36
78.0	0.49	22.76
78.6	0.64	14.41
79.2	0.52	18.34
79.8	0.53	16.87
80.4	0.52	21.96
81.0	0.67	17.11
81.6	6.78	1.71
82.2	21.03	0.31
82.8	31.04	0.09
83.4	38.68	0.06
84.0	44.72	0.12
84.6	49.59	0.17
85.2	53.87	0.13
85.8	57.26	0.07
86.4	60.10	0.05
87.0	62.80	0.03
87.6	65.03	0.01
88.2	67.02	0.03
88.8	68.86	0.04
90.0	70.42	0.17